

9W

VT-709 9W LED WALL LIGHT COLORCODE:4000K IP20 BLACK BODY

Lumens <b>990</b>	Beam Angle <b>360</b>	Dimensions <b>440x335x75mm</b>
----------------------	--------------------------	-----------------------------------

Day White  
 SKU:8224

**2 YEARS**  
 WARRANTY




### Technical Information

Watts:	9	Dimmable:	No
Lumens:	990	Warranty (Years):	2
Beam Angle:	360	PF:	>0.45
Unit Color:	Black	CR:	>80
Body Type:	Aluminium	Operation Temperature:	-25 to +50°C
Long life:	20,000 Hours	Input Power:	AC:220-240V,50/60Hz
IP Rating:	IP20		

### Features

- ✓ Perfect choice of Interior lighting in for fabulous aesthetics and appeal
- ✓ High quality LED chips for a reliable lighting effect
- ✓ Efficient LED Driver & intruded heat sink for reliable lifespan
- ✓ Portability and ease of maintenance
- ✓ Available in different color options - Warm White and Day White
- ✓ Applications - Residential, Building, Restaurants, Décor etc

Note:  Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

### Unit Details

Gross Weight(GW) Kgs	2.115
Unit CBM	0.01786

### Listing Details

EAN Code	3800157623414
Commodity Code	9405403990

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	10
Qty Per Pallet	80

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER

**70**

COUNTRIES