



**12W**

VT-712 12W LED WALL LIGHT COLORCODE:4000K IP20 WHITE BODY

<b>Lumens</b> <b>1100</b>	<b>Beam Angle</b> <b>360</b>	<b>Dimensions</b> <b>260x125x55mm</b>
------------------------------	---------------------------------	--

Day White  
 SKU:8203




## Technical Information

Instant Start: 0-100% in 1/10s	Dimmable: No
Watts: 12	Warranty (Years): 2
Lumens: 1100	PF: >0.5
Beam Angle: 360	CRI: >80
Unit Color: White	Operation Temperature: -20 to +45°C
Body Type: Aluminium + Acrylic	Input Power: AC:220-240V,50/60Hz
Long life: 20,000 Hours	Sensor Compatibility: Yes
IP Rating: IP20	

## Features

- ✓ Perfect choice of Interior lighting for fabulous aesthetics and appeal
- ✓ High quality LED chips for a reliable lighting effect
- ✓ Efficient LED Driver & intruded heat sink for reliable lifespan
- ✓ Portability and ease of maintenance
- ✓ Available in different color options - Warm White and Day White
- ✓ Applications - Residential, Building, Restaurants, Décor etc

Note:  Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

### Unit Details

Gross Weight(GW) Kgs	1.13
Length(Box)mm	280
Width(Box)mm	145
Height(Box)mm	75
Unit CBM	0.003045

### Master Box Packaging

Inner Box Qty	20
Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	320

### Listing Details

EAN Code	3800157623209
Commodity Code	9405403990

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER

**70**

COUNTRIES