



**24W**  
VT-525 24W LED EMERGENCY KIT

Dimensions  
**465 x52x33mm**

SKU:8275

**2** YEARS  
WARRANTY

## Technical Information

Output Voltage: **DC 20-80V**

Watts: **24**

Battery Type: **Ni-Cd7.2V/2000mAh**

Working Time: **3 hours**

Charging Time: **24 hours**

Unit Color: **Silver**

Body Type: **Aluminium**

IP Rating: **IP20**

Dimmable: **No**

Warranty (Years): **2**

Input Power: **AC:220-240V,50/60Hz**

## Features

- ✓ Reliable 3 Hours emergency operation time
- ✓ Sealed Ni-cd battery guarantees high efficiency and lifecycle
- ✓ Output power max 4W
- ✓ AC wire Length 35cm - DC wire length 40 cm
- ✓ Wire length of LED Indicator and Test button 60 cm
- ✓ Compatible only with 6 to 24W V-TAC LED Panel
- ✓ Warranty up to 2 Years

## Packaging

### Unit Details

Gross Weight(GW) Kgs	0.659
Length(Box)mm	75
Width(Box)mm	370
Height(Box)mm	45
Unit CBM	0.00124875

### Listing Details

EAN Code 3800157627474

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	50
Qty Per Pallet	500

READY STOCKS IN  
**UK & EU**



Dispatch within  
24 Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES