



4W

VT-704 4W LED WALL LIGHT COLORCODE:4000K IP65 WHITE BODY SQUARE

Lumens 440	Beam Angle 360	Dimensions 150x150x50mm
----------------------	--------------------------	-----------------------------------

Day White
 SKU:8210



Technical Information

Instant Start: 0-100% in 11s	IP Rating: IP65
Watts: 4	Dimmable: No
Lumens: 440	Warranty (Years): 2
Shape: Square	PF: >0.5
Beam Angle: 360	CRI: >80
Unit Color: White	Operation Temperature: -25 to +50°C
Body Type: Aluminium + Acrylic	Input Power: AC:220-240V,50/60Hz
Long life: 20,000 Hours	Sensor Compatibility: Yes

Features

- ✓ Perfect choice for Interior and Exterior aesthetics
- ✓ Wall washer to create attractive beam designs
- ✓ High quality LED Chips for reliable lighting effect
- ✓ IP65 rated solid ingress protection
- ✓ Glass screen for controlled light beams
- ✓ Available in different color options - Warm White and Day White
- ✓ Applications - Outdoor, Façade, Residential, Restaurants, Building and many more



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.904
Length(Box)mm	160
Width(Box)mm	180
Height(Box)mm	55
Unit CBM	0.001584

Listing Details

EAN Code	3800157623278
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	720

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES