



9W

VT-710 9W LED WALL LIGHT COLORCODE:3000K IP20 WHITE BODY

Lumens 990	Beam Angle 360	Dimensions 210x80mm
----------------------	--------------------------	-------------------------------

Warm White
 SKU:8225

2 YEARS
 WARRANTY

SENSOR
 COMPATIBLE




Technical Information

Instant Start: 0-100% in 1/1s	Dimmable: No
Watts: 9	Warranty (Years): 2
Lumens: 990	PF: >0.5
Beam Angle: 360	CRI: >80
Unit Color: White	Operation Temperature: -25 to +50°C
Body Type: Aluminium + Acrylic	Input Power: AC:220-240V,50/60Hz
Long life: 20,000 Hours	Sensor Compatibility: Yes
IP Rating: IP20	

Features

- ✓ Perfect choice of Interior lighting for fabulous aesthetics and appeal
- ✓ High quality LED chips for a reliable lighting effect
- ✓ Efficient LED Driver & intruded heat sink for reliable lifespan
- ✓ Portability and ease of maintenance
- ✓ Available in different color options - Warm White and Day White
- ✓ Applications - Residential, Building, Restaurants, Décor etc

Note:  Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.8
Length(Box)mm	220
Width(Box)mm	220
Height(Box)mm	100
Unit CBM	0.00484

Listing Details

EAN Code	3800157623421
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	320

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES