



**13.50W**

VT-813 13.5W LED WALL LAMP COLORCODE:4000K BLACK

<b>Lumens</b> 1080	<b>Beam Angle</b> 100	<b>Dimensions</b> 600x100x94mm
-----------------------	--------------------------	-----------------------------------

Day White  
 SKU:8273




## Technical Information

Instant Start:	0-100% in 1/1s	IP Rating:	IP20
Watts:	13.5000	Dimmable:	No
Lumens:	1080	Warranty (Years):	3
Beam Angle:	100	PF:	>0.5
Unit Color:	Black	CRI:	>80
Body Type:	Plastic + Metal	Operation Temperature:	-20 to +45°C
Long life:	30,000 Hours	Input Power:	AC 220-240V, 50/60Hz
LED Chip Type:	SMD	Sensor Compatibility:	Yes

## Features

- ✓ Perfect choice of Interior lighting for fabulous aesthetics and appeal
- ✓ High quality LED chips for a reliable lighting effect
- ✓ Efficient LED Driver & intruded heat sink for reliable lifespan
- ✓ Portability and ease of maintenance
- ✓ Available in different color options - Warm White and Day White
- ✓ Applications - Residential, Building, Restaurants, Décor etc

Note:  Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

# Packaging

## Unit Details

Gross Weight(GW) Kgs	0.891
Length(Box)mm	110
Width(Box)mm	600
Height(Box)mm	90
Unit CBM	0.00594

## Listing Details

EAN Code	3800157627238
Commodity Code	9405403990

## Master Box Packaging

Master Box Qty (Pcs Per Carton)	12
Qty Per Pallet	240

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES