



9W

VT-810 9W LED WALL LAMP COLORCODE:3000K BLACK

Lumens 720	Beam Angle 100	Dimensions 400x100x94mm
----------------------	--------------------------	-----------------------------------

Warm White
 SKU:8267



Technical Information

Instant Start:	0-100% in 11s	IP Rating:	IP20
Watts:	9	Dimmable:	No
Lumens:	720	Warranty (Years):	3
Beam Angle:	100	PF:	>0.5
Unit Color:	Black	CRI:	>80
Body Type:	Plastic + Metal	Operation Temperature:	-20 to +45°C
Long life:	30,000 Hours	Input Power:	AC 220-240V, 50/60Hz
LED Chip Type:	SMD	Sensor Compatibility:	Yes

Features

- ✓ Perfect choice of Interior lighting for fabulous aesthetics and appeal
- ✓ High quality LED chips for a reliable lighting effect
- ✓ Efficient LED Driver & intruded heat sink for reliable lifespan
- ✓ Portability and ease of maintenance
- ✓ Available in different color options - Warm White and Day White
- ✓ Applications - Residential, Building, Restaurants, Décor etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.612
Length(Box)mm	110
Width(Box)mm	400
Height(Box)mm	100
Unit CBM	0.0044

Listing Details

EAN Code	3800157627177
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	12
Qty Per Pallet	240

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES