



6W

VT-836 6W LED WALL LIGHT COLORCODE:3000K -WHITE BODY

Lumens 660	Beam Angle 90	Dimensions 112x112x93mm
----------------------	-------------------------	-----------------------------------

Warm White
 SKU:8301



Technical Information

Instant Start:	0-100% in 11s	IP Rating:	IP65
Watts:	6	Dimmable:	No
Lumens:	660	Warranty (Years):	2
Beam Angle:	90	PF:	>0.5
Unit Color:	White	CRI:	>80
Body Type:	Aluminium	Operation Temperature:	-20 to +45°C
Long life:	20,000 Hours	Input Power:	AC:220-240V,50/60Hz
LED Chip Type:	SMD	Sensor Compatibility:	Yes

Features

- ✓ High Quality Bridgelux chips for reliable operation and lifetime
- ✓ Get range of up-down beams with Adjustable beam angle to feel range of aesthetics
- ✓ Constructed to high quality aluminum for efficient heat dissipation
- ✓ Cylindrical & Cubical fixtures in 3 colors to fit into range of architectural structures
- ✓ Elegant replacement for traditional up-down lighting
- ✓ Application: Perfect for living rooms, pathways, balconies, facades etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.75
Unit CBM	0.001728

Listing Details

EAN Code	3800157629959
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	720

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES