



10W

VT-811 10W LED WALL LIGHT COLORCODE:3000K -WHITE BODY

Lumens 1100	Beam Angle 360	Dimensions 300x215x60mm
-----------------------	--------------------------	-----------------------------------

Warm White
 SKU:8307




Technical Information

Watts:	10	Dimmable:	No
Lumens:	1100	Warranty (Years):	2
Beam Angle:	360	PF:	>0.45
Unit Color:	White	CRI:	>80
Body Type:	Aluminium	Operation Temperature:	-20 to +45°c
Long life:	20,000 Hours	Input Power:	AC:110-240V,50/60Hz
LED Chip Type:	SMD	Sensor Compatibility:	Yes
IP Rating:	IP65		

Features

- ✓ Perfect choice of Interior lightingin for fabulous aesthetics and appeal
- ✓ High quality LED chips for a reliable lighting effect
- ✓ Efficient LED Driver & intruded heat sink for reliable lifespan
- ✓ Portability and ease of maintenance
- ✓ Available in different color options - Warm White and Day White
- ✓ Applications - Residential, Building, Restaurants, Décor etc

Note:  Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	1.157
Unit CBM	0.004991

Listing Details

EAN Code	3800157630016
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	240

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES