



6W

VT-606RD 6W LED PREMIUM PANEL WITH SAMSUNG CHIP
 COLORCODE:4000K ROUND

Lumens 420	Beam Angle 120	Dimensions ?120x12mm
----------------------	--------------------------	--------------------------------

Day White
 SKU:707



Technical Information

Instant Start:	0-100% lt1Sec	LED Chip Type:	SMD
Output Voltage:	DC:12-24V	IP Rating:	IP20
Watts:	6	Dimmable:	No
Lumens:	420	Warranty (Years):	5
Shape:	Round	PF:	>0.5
Beam Angle:	120	CRI:	>80
Cutting Size:	?110mm	Operation Temperature:	-20°C to 45°C
Unit Color:	White	Input Power:	AC:85-265V,50/60Hz
Body Type:	Aluminium	Sensor Compatibility:	Yes
Long life:	20,000 Hours		

Features

- ✓ Contemporary & Elegant Design
- ✓ Highly Efficient LED Samsung Chip
- ✓ Easy to install - Plug & Play
- ✓ High-quality power driver ensures a reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ No Lead or Mercury content hence Environment-friendly
- ✓ Easy to install & Low Maintenance
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.205
Unit CBM	0.000756

Listing Details

EAN Code	3800157641630
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	40
Qty Per Pallet	1600

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES