



## 24W

VT-624SQ 24W LED PREMIUM PANEL WITH SAMSUNG CHIP  
 COLORCODE:6400K SQUARE

Lumens <b>2000</b>	Beam Angle <b>120</b>	Dimensions <b>?300x300x12mm</b>
-----------------------	--------------------------	------------------------------------

White  
 SKU:723



## Technical Information

Output Voltage:	DC:54-100V	LED Chip Type:	SMD
Watts:	24	IP Rating:	IP20
Lumens:	2000	Dimmable:	No
Shape:	Square	Warranty (Years):	5
Beam Angle:	120	PF:	>0.9
Cutting Size:	?280x280mm	CRI:	>80
Unit Color:	White	Operation Temperature:	-20°C to 45°C
Body Type:	Aluminium	Input Power:	AC:85-265V,50/60Hz
Long life:	30,000 Hours	Sensor Compatibility:	Yes

## Features

- ✓ Contemporary & Elegant Design
- ✓ Highly Efficient LED Samsung Chip
- ✓ Easy to install - Plug & Play
- ✓ High-quality power driver ensures a reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ No Lead or Mercury content hence Environment-friendly
- ✓ Easy to install & Low Maintenance
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

### Unit Details

Gross Weight(GW) Kgs	1.04
Unit CBM	0.00433

### Listing Details

EAN Code	3800157641791
Commodity Code	9405403990

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	10
Qty Per Pallet	300

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES