



12W

VT-827 12W LED WALL LIGHT COLORCODE:4000K,BLACK -SQUARE

Lumens 650	Beam Angle 128	Dimensions 169x100mm
----------------------	--------------------------	--------------------------------

Day White
 SKU:8540



Technical Information

Output Voltage:	DC:36-40V
Watts:	12
Lumens:	650
Shape:	Square
Beam Angle:	128
Output Current:	280mA
No. Of Led:	72
Unit Color:	Black
Body Type:	PC
Long life:	20,000 Hours

LED Chip Type:	SMD
IP Rating:	IP65
Dimmable:	No
Warranty (Years):	2
PF:	>0.5
CRI:	>80
Operation Temperature:	-25 to +50°C
Input Power:	AC:220-240V,50/60Hz
Sensor Compatibility:	Yes

Features

- ✓ Modern Wall lights available in sleek and stylish designs.
- ✓ Excellent heat dissipation
- ✓ Available in different color options - Warm White and Day White
- ✓ Easy installation and Maintenance
- ✓ Application: Perfect for halls, pathways, Bedroom, Kitchen etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.72
Unit CBM	0.00289

Listing Details

EAN Code	3800157638890
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	400

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES