



## 12W

VT-759-12 12W-WALL LAMP WITH BRIDGELUX CHIP COLORCODE:3000k WHITE SQUARE

Lumens <b>1100</b>	Beam Angle <b>120</b>	Dimensions <b>100x100x100mm</b>
-----------------------	--------------------------	------------------------------------

Warm White  
 SKU:8527



## Technical Information

Watts:	12	LED Chip Type:	SMD
Lumens:	1100	IP Rating:	IP65
Shape:	Square	Dimmable:	No
On/Off Cycles:	>15000	Warranty (Years):	2
Beam Angle:	120	PF:	>0.45
Unit Color:	White	CRI:	>80
Body Type:	Aluminium	Input Power:	AC:220-240V,50/60Hz
Long life:	20,000 Hours	Sensor Compatibility:	Yes

## Features

- ✓ High Quality Bridgelux chips for reliable operation and lifetime
- ✓ Get range of up-down beams with Adjustable beam angle to feel range of aesthetics
- ✓ Constructed to high quality aluminum for efficient heat dissipation
- ✓ Cylindrical & Cubical fixtures in 3 colors to fit into range of architectural structures
- ✓ Elegant replacement for traditional up-down lighting
- ✓ Application: Perfect for living rooms, pathways, balconies, facades etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

### Unit Details

Gross Weight(GW) Kgs	0.7
Unit CBM	0.001331

### Listing Details

EAN Code	3800157638616
Commodity Code	9405403990

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	1000

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER

**70**

COUNTRIES