



18W

VT-619SQ 18W LED ADJUSTABLE PANEL WITH SAMSUNG CHIP
COLORCODE:3000K SQUARE

Lumens 1350	Beam Angle 120	Dimensions 170x170x32mm
-----------------------	--------------------------	-----------------------------------

Warm White
SKU:736

5 YEARS
WARRANTY



SENSOR
COMPATIBLE



Technical Information

Instant Start:	0-100% 1t1Sec
Watts:	18
Lumens:	1350
Shape:	Square
On/Off Cycles:	>15000
Beam Angle:	120
Cutting Size:	75-100mm
Unit Color:	White
Body Type:	Aluminium
Long life:	20,000 Hours

LED Chip Type:	SMD
IP Rating:	IP20
Dimmable:	No
Warranty (Years):	5
PF:	>0.6
CRI:	>80
Operation Temperature:	-20°C to 45°C
Input Power:	AC:85-265V,50/60Hz
Sensor Compatibility:	Yes

Features

- ✓ Contemporary & Elegant Design
- ✓ Highly Efficient LED Samsung Chip
- ✓ Easy to install - Plug & Play
- ✓ High-quality power driver ensures a reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ No Lead or Mercury content hence Environment-friendly
- ✓ Easy to install & Low Maintenance
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs 0.385

Unit CBM 0.002815

Listing Details

EAN Code 3800157643054

Commodity Code 9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton) 20

Qty Per Pallet 600

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES