



**12W**

VT-610RD 12W LED ADJUSTABLE PANEL WITH SAMSUNG CHIP  
 COLORCODE:6400K ROUND

Lumens <b>750</b>	Beam Angle <b>120</b>	Dimensions <b>D:120x32mm</b>
----------------------	--------------------------	---------------------------------

White  
 SKU:729



## Technical Information

Instant Start:	0-100% 1t1Sec
Watts:	12
Lumens:	750
Shape:	Round
On/Off Cycles:	>15000
Beam Angle:	120
Cutting Size:	75-100mm
Unit Color:	White
Body Type:	Aluminium
Long life:	20,000 Hours

LED Chip Type:	SMD
IP Rating:	IP20
Dimmable:	No
Warranty (Years):	5
PF:	>0.6
CRI:	>80
Operation Temperature:	-20°C to 45°C
Input Power:	AC:85-265V,50/60Hz
Sensor Compatibility:	Yes

## Features

- ✓ Contemporary & Elegant Design
- ✓ Highly Efficient LED Samsung Chip
- ✓ Easy to install - Plug & Play
- ✓ High-quality power driver ensures a reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ No Lead or Mercury content hence Environment-friendly
- ✓ Easy to install & Low Maintenance
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

### Unit Details

Gross Weight(GW) Kgs	0.256
Unit CBM	0.00153

### Listing Details

EAN Code	3800157642989
Commodity Code	9405403990

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	640

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER

**70**

COUNTRIES