



24W

VT-625RD 24W LED ADJUSTABLE PANEL WITH SAMSUNG CHIP
 COLORCODE:3000K ROUND

Lumens 1800	Beam Angle 120	Dimensions D:223x32mm
-----------------------	--------------------------	---------------------------------

Warm White
 SKU:739



Technical Information

Instant Start: 0-100% 1t1Sec	LED Chip Type: SMD
Watts: 24	IP Rating: IP20
Lumens: 1800	Dimmable: No
Shape: Round	Warranty (Years): 5
On/Off Cycles: >15000	PF: >0.6
Beam Angle: 120	CRI: >80
Cutting Size: 75-200mm	Operation Temperature: -20°C to 45°C
Unit Color: White	Input Power: AC:85-265V,50/60Hz
Body Type: Aluminium	Sensor Compatibility: Yes
Long life: 20,000 Hours	

Features

- ✓ Contemporary & Elegant Design
- ✓ Highly Efficient LED Samsung Chip
- ✓ Easy to install - Plug & Play
- ✓ High-quality power driver ensures a reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ No Lead or Mercury content hence Environment-friendly
- ✓ Easy to install & Low Maintenance
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.7245
Unit CBM	0.004421

Listing Details

EAN Code	3800157643085
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
---------------------------------	----

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES