



**12W**

VT-610SQ 12W LED ADJUSTABLE PANEL WITH SAMSUNG CHIP  
COLORCODE:4000K SQUARE

Lumens <b>750</b>	Beam Angle <b>120</b>	Dimensions <b>120x120x32mm</b>
----------------------	--------------------------	-----------------------------------

Day White  
SKU:731

**5 YEARS**  
WARRANTY



**SENSOR**  
COMPATIBLE



## Technical Information

Instant Start: 0-100% 1t1Sec	LED Chip Type: SMD
Watts: 12	IP Rating: IP20
Lumens: 750	Dimmable: No
Shape: Square	Warranty (Years): 5
On/Off Cycles: >15000	PF: >0.6
Beam Angle: 120	CRI: >80
Cutting Size: 75-100mm	Operation Temperature: -20°C to 45°C
Unit Color: White	Input Power: AC:85-265V,50/60Hz
Body Type: Aluminium	Sensor Compatibility: Yes
Long life: 20,000 Hours	

## Features

- ✓ Contemporary & Elegant Design
- ✓ Highly Efficient LED Samsung Chip
- ✓ Easy to install - Plug & Play
- ✓ High-quality power driver ensures a reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ No Lead or Mercury content hence Environment-friendly
- ✓ Easy to install & Low Maintenance
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

### Unit Details

Gross Weight(GW) Kgs	0.295
Unit CBM	0.00153

### Listing Details

EAN Code	3800157643009
Commodity Code	9405403990

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	800

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES