



45W

VT-646 45W LED PANEL LIGHT-1200x600 WITH SAMSUNG CHIP
COLORCODE:4000K 5 YRS WARRANTY

Lumens 5400	Beam Angle 120	Dimensions 595x1195mm
-----------------------	--------------------------	---------------------------------

Day White
SKU:748

5 YEARS
WARRANTY



SENSOR
COMPATIBLE



Technical Information

Instant Start:		LED Chip Type:	SMD-Samsung Chip
Watts:	45	IP Rating:	IP20
Lumens:	5400	Dimmable:	No
Shape:	Rectangle	Warranty (Years):	5
On/Off Cycles:	>10000	PF:	>0.9
Beam Angle:	120	CRI:	>80
Unit Color:	White	Operation Temperature:	-20°C to +45°C
Body Type:	Aluminium + PMMA + PP	Input Power:	DC:30-42V,50Hz
Long life:	30,000 Hours	Sensor Compatibility:	Yes

Features

- ✓ Contemporary & Elegant Design
- ✓ Highly Efficient LED Samsung Chip
- ✓ Higher Light Transmission Rate
- ✓ Quick connector making the installation easy - Plug & Play
- ✓ High quality power driver ensures reliable lifetime - Smart Driver Box
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ Strong Aluminium body and efficient heat dissipation
- ✓ No Lead or Mercury content hence Environment friendly
- ✓ Easy to install & Low Maintenance
- ✓ Complies with LM-80
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	8.53
Unit CBM	0.055633

Listing Details

EAN Code	3800157636315
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	2
---------------------------------	---

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES