
















ROHS-COMPLIANT



LTR	REV.	DESCRIPTION	DATE
	C	ECR # 061123-5 ADD LENGTH	11/23/06
	D	ECR # 061218-6 ADD CABLE P/N	12/18/06



NOTE:

- CABLE: UL 2919[30AWG(7/0.102 T.C)*1C INS: FOAM-PE ID:1.3±0.05 + SPIRAL(T.C)]*3C INS: PVC ID:2.3±0.1+28AWG(7/0.127 T.C)*7C + INS:SR-PVC ID:ø0.9±0.05mm+AL/MY+DRAIN 30AWG(7/0.102 T.C) + BRAID (16/4/0.1 T.C)+OUTER JACKET: PVC COLOR: BLACK(NK-K01) OD:ø7.5±0.15mm, **(C2919283BA)** 
- CONNECTOR:
P1&P2: HDB 15P MALE, GOLD FLASH CONTACT, NICKEL PLATED SHELL.
9TH PIN IS EMPTY.
- FERRITE CORE: 17.5*28.5*9.5mm.
- SHIELD: COPPER-FOIL 360° SOLDERED TO CONNECTOR SHELL & CABLE BRAID.
- HOOD: MOLDED TYPE, PVC 45P, COLOR: BLACK(NK-K01).
- ELECTRICAL TEST: 100% OPEN SHORT MIS WIRE TEST . CONTACT RESISTANCE 3Ω MAX INSULATION RESISTANCE 10MΩ MIN
- PACKING: <1>EACH PC / POLYBAG + EAN CODE LABEL & ROHS LABEL <2>EACH CARTON / ROHS LABEL(L*W=35*22mm)

PIN OUT		P1		P2	
1		1	ORANGE	10	ORANGE
2		2	WHITE	11	WHITE
3		3	YELLOW	12	YELLOW
4		4	GREEN	13	GREEN
5		5	RED	14	RED
6		6	BRAID	14	BRAID
7		7	SHELL	14	SHELL
8		8	CENTER		
9		9	SHIELDING		

120-2620-6	CY0018	20000±200mm	4260113562994	
120-2620-5	CY0017	15000±150mm	4260113562512	
120-2620-4	CY0016	10000±100mm	4260113562505	
120-2620-3	CY0003	5000±50mm	4260113560204	
120-2620-2	CY0002	3000±30mm	4260113560198	
120-2620-1	CY0001	1800±30mm	4260113560181	
DWG	P/N	L±T	EAN CODE	

Tolerance	Inch	M/M	Title	
X	.015	.30	2D IRECT G MBH	
.XX	.010	.10	HDB 15M/M CABLE	
.XXX	.005	.05		
Draw	Customer P/N			
FANNIE	12/18/06			
App'd	Customer	P/N	Customer	E-DIR
Scale	NONE	Units	m/m	Third Angle Projection
Dwg No.	120-2620	REV:ID	Sheet	1/2