

Within Series Adaptor 32_MBX-50-0-2/111_N

Description

Adaptor plug/plug
MBX plug (male) / MBX plug (male)

Slide - snap interface

Interface standard
Series MBX - HUBER+SUHNER MBX



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Number of matings 100
Weight 0.000881 kg

Environmental Data

Operating temperature -55 °C to 155 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Interface - MBX plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze	SUCOPRO Plating
Body	Bronze	Gold Plating
Insulator	PFA / PTFE / LCP	

Interface - MBX plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze	SUCOPRO Plating
Body	Bronze	Gold Plating
Insulator	PFA / PTFE / LCP	

Related Documents

Outline drawing DOU-00145547

Ordering Information

Bulk 100 pcs package 32_MBX-50-0-2/111_NH
Single package 32_MBX-50-0-2/111_NE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[32_MBX-50-0-2/111_NE](#)