

## Within Series Adaptor 34\_BNC-75-0-1/133\_N

### Description

Bulkhead adaptor jack/jack  
BNC jack (female) / BNC jack (female)

Interface standard  
Series BNC - Compatible with IEC 61169-8\_MIL-STD-348A/301\_CECC 22120



### Technical Data

#### Electrical Data

Impedance 75 Ω  
Interface frequency max. 1 GHz

#### Mechanical Data

Number of matings 500  
Weight 0.0169 kg

#### Environmental Data

Operating temperature -65 °C to 165 °C  
2011/65/EU (RoHS - including 2015/863 and 2017/2102) compliant

#### Material Data

Interface - BNC jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	

Interface - BNC jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

### Related Documents

Catalogue drawing DCA-00013669  
Mounting hole DOU-00008751

### Ordering Information

Single package 34\_BNC-75-0-1/133\_NE  
Bulk 100 pcs package 34\_BNC-75-0-1/133\_NH