

## Han M Hood Top Entry 2 Pegs PG 11



Image is for illustration purposes only. Please refer to product description.

Part number	09 37 003 1440
Specification	Han M Hood Top Entry 2 Pegs PG 11
HARTING eCatalogue	<a href="https://b2b.harting.com/09370031440">https://b2b.harting.com/09370031440</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> M
Type of hood/housing	Hood

### Version

Locking type	Single locking lever
Size	3 A
Version	Top entry
Cable entry	1x Pg 11
Field of application	Hoods/housings for rough environments

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance

## Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Approvals	DNV GL
CE	Yes

## Commercial data

Packaging size	10
Net weight	65.16 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09370031440](#)