

SENCITY® Spot-S WiFi Dual-Band Antenna 1399.17.0210

Description

Small directional, planar, linear polarized dual-band WiFi antenna with 9 dBi gain
 WiFi bands 2.4 to 2.5 GHz and 5.150 to 5.975 GHz on one single port
 WLAN IEEE 802.11 a/b/g/h/p
 Rugged design, meets EN 50155 railway and EN 60068 industrial standards
 Fire retardant acc. to EN 45545-2 and NFPA130
 For outdoor and indoor applications
 Ingress protection IP 66 and IP 67

Wall mounting material included



Product Configuration

Technical Data

Electrical Data

	Band 1	Band 2
Frequency (MHz)	2400 - 2500	5150 - 5935
VSWR	2	2
Impedance (Ohm)	50	50
Gain (dBi)	9	9
3dB beamwidth (h) (°)	75	45
3dB beamwidth (v) (°)	65	30
Composite power max (W)	30	30
Ambient temperature (°C)	25	25
Front to back ratio (dB)	15	15
Port Isolation (dB)	25	30

Ports

	Port 1
Connector	N, jack (female)
Polarization	vertical
DC grounded	No

Connections

	Band 1	Band 2
Port 1	X	X

General Data

Mechanical Data

Dimensions (mm) 101 x 81 x 36 (Height x Width x Depth)
 Weight (kg) 0.11
 Windload frontal: 15 N at 160 km/h , Wind speed survival: 220 km/h
 Included mounting material Wall mounting material

Environmental Data

Environmental conditions indoor/outdoor
 Operation temperature (°C) -40 to 85
 Storage temperature (°C) -40 to 85
 Transport temperature (°C) -40 to 85
 Flammability rating EN 45545-2
 2011/65/EU (RoHS - including 2015/863 and 2017/2102) compliant
 Lead-free soldered yes

SENCITY® Spot-S WiFi Dual-Band Antenna 1399.17.0210

WEEE 2012/19/EU
REACH 1907/2006/EC

special marking needed
compliant

FLAMMABILITY: EN 45545-2 (2013) HL3 and NFPA130 (2013), also BS 6853 and DIN 5510-2
ENVIRONMENT: Meets EN 50155 (2016) and EN 60068 related tests

IP RATING: IP 66 / IP 67 (IEC 60529)

SOLAR RADIATION: EN 50125-3:2004 §4.9, 1120 W/m² for 20h

AIR PRESSURE: EN 50125-3:2004 §4.2, Altitude Class A1 (up to 1400m)

AIR PULSE PRESSURE: EN 50125-3:2004 §4.2, 1 kPa/s

RAIN: EN 50125-3:2004 §4.6, delivery rate: 6 mm/min

VIBRATION / SHOCK: EN 50125-3:2004 §4.13, position profile: "outside the track"

POLLUTION: EN 50125-3:2004 §4.11, pollution levels: 4B1, 4S1

CORROSION: MIL-F-14072 E Type 1 "exposed"

MECHANICAL IMPACT (HAMMER IMPACT): EN 60068-2-75 (IEC 62262/2002-02 IK06)

Material Data

Radome colour RAL 7044 (grey)
Radome material PC (Polycarbonate)

Related Products

9091.99.0238 Outdoor Spot-S Antenna Down-Sidetilt Bracket

9091.99.0237 L-Bracket for SPOT-S antennas

Related Documents

Mounting instruction DOC-0000287053
Painting instruction DOC-0000278984
Security instruction DOC-0000278984
Outline drawing DOU-00168098.1
3D-model DOC-0000384130

Additional Information

Following Declaration of Conformity for SENCITY Spot-S antennas are available on request: * Industrial standards EN 60068 / EN 60529 / IEC 61373: Ref. DOC-0000318049 * Railway rolling stock, environmental standards EN 50155 and fire behaviour EN 45545-2k, NFPA130: Ref. DOC-0000380375