

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010420](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect Turned Crimp Contact for 40A Inserts and Modules, Male, Silver (Ag) Plated Copper Alloy, 4.00mm² (12 AWG), 100 per Bag

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification 936010406-S00 \(PDF\)](#)

Agency Certification

CSA 256883
 UL E249674

General

Product Family Industrial Connectors / Enclosures
 Series [93601](#)
 Contact Type Turned Crimp
 Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)
 Product Category Contacts
 Product Name GWconnect
 UPC 887191889283

Physical

Gender Male
 Material - Contact Copper Alloy
 Material - Plating Silver
 Net Weight 2.950/g
 Number of Grooves 0
 Packaging Type Bag
 Stripping Length 9.60mm
 Wire Size AWG 12
 Wire Size mm² 4.00

Electrical


Current - Maximum per Contact 40.0A

Material Info

Engineering Number 7600.5712.0

Reference - Drawing Numbers

Product Specification 936010406-S00
 Sales Drawing 936010422-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of Conformity

China RoHS

50 Image

Not Relevant

Not Contained

CER_4000400719_00_000.pdf

Search Parts in this Series

[93601](#) Series

Mates With

[93601](#) Female Turned Crimp Contact

Use With

S-K, S-Q, S-QD, and S-M Inserts