

KombiSIGN 70 / LED Permanent Beacon 843

LED Perm. light element 115VAC GN



Part No.:	843.200.67		NoHS2		UK
Series:	KombiSIGN 70	7	КОП 32	C QL) US	CA

MECHANICAL DATA		
Height	66 mm	
Diameter	70 mm	
Materials	PC	
Dome colour	Green	
Protection category	IP54	
Working temperature minimum	-20°C	
Working temperature maximum	+50°C	
Weight with packaging	83 g	
Product weight	69 g	

ELECTRICAL DATA	
Operating voltage	115V
Operating voltage type	AC
Operating voltage frequency	60Hz
Operating voltage tolerance	+/- 10%
Rated operational voltage	115 VAC
Rated operational current	20 mA
Rated inrush current	500 mA
Protection class	Protection class 2
Pollution degree	3
Overvoltage category	II
Isolation voltage	Ui = 250V; Uimp = 2.500V

OPTICAL DATA		
Light source	LED	
Light colour	Green	
Optical signal image	Permanent	
Service life optical	100,000 h maximum	

APPROVAL DATA		
Conforms with CE	Yes	
WEEE	Yes	
Conforms with RED directive	No	
Conforms with ATEX-directive	No	
Conforms with CCC	No	
Conforms with UL	cULus	
UL Type Rating	Type 12	
Conforms with FCC	No	
Conforms with IC	No	


For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.



KombiSIGN 70 / LED Permanent Beacon 843

LED Perm. light element 115VAC GN

EAC certificate available	Yes
Conforms with UKCA (Importer)	Yes (WERMA (UK) Ltd.)
Conforms with CMIM	No
Conforms with AS-I	No
ICAO Certification	No
Conforms with DNV	No
Conforms with RoHS CN	No
Conforms with VdS	No



For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.