

S/FTP Cat. 6A LSZH patch cord, grey, 7.5 m

PP6A-LSZHCU-7.5M

- Perfect connection
- Dual shielded for a reliable connection
- Low Smoke Zero Halogen (LSZH) jacket
- Gold plated contacts



Features

- Patch cord with foil shielded pairs and braided cable, CAT 6A
- Gold plated contacts
- Low Smoke Zero Halogen (LSZH) jacket
- Molded strain reliefs
- Snagless boots

Packaging

Q'ty in crtn, pcs	50
Crtn volume, CUM	0.038
Crtn weight, kgs	12.35
Individual package size LxWxH:	125x15x170 mm
Carton size LxWxH:	400x290x330 mm
Country of origin	CN
Barcode	8716309125628
Customs code	8544421000

Specifications

Patch cord category 6A SSTP (shielded)
Length: according to the item
Structure: AWG 27 (7 x 0.135 mm wire), COPPER
FM-PE insulation of the wire: 1.0 mm
With LDPE filler
With polyester tape
With aluminum foil
Drain hose: not used
With Braid : 16 x 4/0.12mm
Outer insulation: 5.8 mm
Color: according to the item
Operation up to 500 MHz

Certificates

