

**Model Number: 4G-BA01**

## PRODUCT SPECIFICATION

### I. Main features

#### \*Electrical

No.	Item	Specifications
1	Frequency (MHz)	680-960/1710-2700
2	Gain (Zenith)	6dBi
3	V.S.W.R	<2
4	Impedance	50Ω
5	Max Input Power	50W
6	Lightning protection	DC ground
7	Polarization	V

#### \*Mechanical

No.	Item	Specifications
1	Cable	RG58, 0m/3m/5m or others
2	Connector	Type SMA,N-female, or others
3	Dimensions (cm)	41x21x6,2
4	Weight (kg)	0,5
5	Mounting method	Pole/ Wall mount
6	Plastic Housing	White
7	Working Temperature	-40°C~+85°C
8	Working Humidity	5~95%

## II. Appearance

4G-BA01-0



4G-BA01-1



4G-BA01-2



## III. Engineering drawing



Unit : mm