

## Han CGM-M-Rail M32 D.20.5-25mm



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 7125
Specification	Han CGM-M-Rail M32 D.20.5-25mm
HARTING eCatalogue	<a href="https://b2b.harting.com/19000007125">https://b2b.harting.com/19000007125</a>

### Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> CGM-M-Rail
Type of accessory	Cable gland
Description of the accessory	Railway version

### Technical characteristics

Tightening torque	≤8 Nm (depending on the cable and the seal insert used)
Wrench size	36 40
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP68
Size	M32
Clamping range	20.5 ... 25 mm
Width across corners	43.9 mm

### Material properties

Material (seal)	EPDM
Material (cable glands)	Brass
Surface (accessories)	Nickel plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



Pushing Performance

## Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	10
Net weight	121.3 g
Country of origin	Germany
European customs tariff number	84849000
eCl@ss	27144432 Screwed cable gland (electr.)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19000007125](#)