

## Han CGM-P F+B M25x1,5 D. 13-16 black



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 19 15 503 5197  |
| Specification      | Han CGM-P F+B M25x1,5 D. 13-16 black  |
| HARTING eCatalogue | <a href="https://b2b.harting.com/19155035197">https://b2b.harting.com/19155035197</a> |

### Identification

|                          |                      |
|--------------------------|----------------------|
| Category                 | Accessories          |
| Series of hoods/housings | Han <sup>®</sup> F+B |
| Type of accessory        | Cable gland          |

### Version

|               |                     |
|---------------|---------------------|
| Pack contents | With spacing washer |
|---------------|---------------------|

### Technical characteristics

|  |                 |
|--|-----------------|
| Limiting temperature                   | -40 ... +100 °C |
| Wrench size                            | 32              |
| Degree of protection acc. to IEC 60529 | IP67 / IP69     |
| Size                                   | M25             |
| Clamping range                         | 13 ... 16 mm    |

### Material properties

|                          |  |
|--------------------------|--|
| Roughness of the surface | ≤0.8 µm  |
| Colour (seal)            | Blue   |
| Material (cable glands)  | Polyamide (PA)   |
| Material (accessories)   | VA 1.4305  |
| Colour (accessories)     | Black  |
| RoHS                     | compliant with exemption                               |
| RoHS exemptions          | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status               | compliant with exemption                               |



Pushing Performance

## Material properties

|                             |      |
|-----------------------------|------|
| China RoHS                  | 50   |
| REACH Annex XVII substances | No   |
| REACH ANNEX XIV substances  | No   |
| REACH SVHC substances       | Yes  |
| REACH SVHC substances       | Lead |

## Specifications and approvals

|           |                        |
|-----------|------------------------|
| Approvals | Ecolab Topactive 200   |
|           | Ecolab Topactive 500   |
|           | Ecolab Topax 66        |
|           | Ecolab Topactive OKTO  |
|           | Ecolab Topax 990       |
|           | FDA 21 CFR 177.1500    |
|           | FDA 21 CFR 176.170 (c) |
|           | FDA 21 CFR 177.1390    |
|           | FDA 21 CFR 177.1395    |
|           | FDA 21 CFR 177.2600    |

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 1                                      |
| Net weight                     | 15.37 g                                |
| Country of origin              | Germany                                |
| European customs tariff number | 39174000                               |
| eCl@ss                         | 27144432 Screwed cable gland (electr.) |