



### MATERIALS:

Body and Fittings – Brass per QQ-B-626, Alloy 360, 1/2 Hard.

Center and Outer Contact – Gold plated Beryllium Copper per QQ-C-530 Cond. HT.

Insulator – Teflon

### Finish:

Body and Fittings – Tarnish Resistant Plating

Center and Outer Contact – Gold plated Beryllium Copper

Marking: “POMONA 3580”

### RATINGS:

Operating Temperature: -65°C. (85°F.) to +165° C. (+329°F.)

Dielectric: PTFE

### ORDERING INFORMATION: Model 3580

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ± .005” (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[3580](#)