



LEATHERMAN®

SKELETOOL®



SPECIFICATIONS

Closed Length: 4 in. | 10.16 cm.
Open Length: 6 in. | 15.24 cm.
Primary Blade length: 2.6 in. | 6,6 cm.
Weight: 5 oz. | 142 g.
Width: 1.24 in. | 3,15 cm.
Overall thickness: .52 in. | 1.32 cm.
Materials: 420HC Stainless Steel,

REFERENCE & PACKAGING

830921- PEG
Dimensions 10,25 x 11,25 x 10,63 in
Weight: 6,63lb
EAN: 037447237454

830920- BOX
Dimensions 7,25 x 12,75 x 10,7 in
Weight: 11,80lb
EAN: 0037447202957

TOOLS

- 01 Needlenose Pliers
- 02 Regular Pliers
- 03 Hard-wire Cutters
- 04 Wire Cutters
- 05 420HC Combo Knife
- 06 Carabiner/Bottle Opener
- 07 Large Bit Driver

INCLUDED BITS: Phillips #1 & #2,
Screwdriver 1/4" & 3/16



At a mere five ounces, the Leatherman Skeletool has a stainless steel combo blade, pliers, bit driver, removable pocket clip and carabiner/bottle opener. The Skeletool is just what you need in one good lookin' package.



Distributeur Exclusif
Tél: +33 3 20 68 57 00
Fax: +33 3 20 36 52 30
email: service@gmtoutdoor.fr -
www.gmtoutdoor.fr

OUR WARRANTY: We pride ourselves on offering high-quality products made in our Portland, Oregon, USA factory, which is why we offer our 25-year warranty, so you can be sure your Leatherman will last a lifetime. If you need it fixed, just return it and we'll take care of the repair.