

OVERLOAD SWITCH

Specifications

1. Size:


Table 1 (Unit:mm)

KLS P/N	Rated Current	Applications	Note
L-KLS7-ST-003-05	1.5-16A 250 V 50Hz	Dc motor, AC motor, Home Appliances	

Current Loading(Rated Current Percentage)

2. Technical Characteristic (Test in 20-25°C), see the graph below

Short circuit test, environment temperature:25°C



Current Loading (%)	Tripping Time
100 %	Hold, No-Trip
150 %	Trip within 1 Hour
200 %	3.0-30S
300 %	0.8-8S
400 %	0.35-5S
500 %	0.3-2.8S
600 %	0.25-2S
800 %	0.2-1S
1000 %	0.15-0.8S