

Specifications	UTi120Mobile
Certifications	CE, FCC, RoHS
IR resolution	120×90 pixels
Field of view (FOV)	50°×38°
Thermal sensitivity (NETD)	< 60mk
Temperature range	-20~400°C
Emissivity	0.1-0.99(adjustable)
Frame rate	25Hz
Measurement accuracy	±2°C or ±2% whichever is greater
Display modes	Thermal, blending(blend with image of mobile phone ), PIP
Image capturing modes	Take photos or videos
Plate	Iron Red, Rainbow, Gray scale, Red hot, Black White, Lava, High-Contrast Rainbow
Image format	JPG
Data communication	Type-C USB
Drop proof	2m
General Characteristics	
Product color	Black and grey
Product net weight	25g
Product size	53X18.2X18.5mm
Standard accessories	Type-C male to female extension cable, USB adapter
Standard individual packing	Gift box, English manual
Standard quantity per carton	20
Standard carton measurement	290×265×325mm