

Specifications	UTi120P
Certification	CE, RoHS
IR resolution	120 x 90 pixels
Field of view (FOV)	51° x 38°
Thermal sensitivity (NETD)	<60mk
Temperature range	-20~400°C
Spatial resolution (IFOV)	7.3mrad
Frame rate	25Hz
Measurement accuracy	±2°C or ±2% whichever is greater
Palettes	3
Emissivity	Adjustable (0.01-1.00)
Focus	Focus free
Display modes	Thermal
Display	2.4" TFT LCD
Auto capture of Hi/Lo temperature	√
Measurement modes	Point, area
PC analysis software	√
Drop proof	1m
General Characteristics	
Power	Li-ion battery (3.7V 1300mAh);
Product net weight	125g
Product size	76mm x 76 mm x 22mm
Standard accessories	Carrying bag, micro USB cable, micro SD card, English manual
Standard individual packing	Blister, gift box
Standard quantity per carton	5pcs
Standard carton measurement	390mm x 130mm x 140mm
Standard carton gross weight	2.8kg