

# Cat 6A Ethernet Cable

- 500 MHz Performance Speeds
- Ideal for 100BASE-TX and 10GBASE-T (10-Gigabit Ethernet)
- Rated for More than 10 Million Flexing Cycles
- Exceptional EMI/RFI Suppression
- Rated for Temperatures from -65°C to +165°C

Cicoil's Cat 6A Ethernet Cable meets the increased demands of professionals who need a rugged, flexible and high performance Ethernet cable solution. Cicoil's patented extrusion process allows individually shielded, twisted pairs to be placed in a flexible flat profile for high speed data transmission, with exceptional EMI/ RFI suppression. Cicoil's Cat 6A Flat Cable delivers the ultimate in electrical performance, extreme ruggedness, and a Flex rating of over 10 Million cycles.



## Cable

Amp Rating <sup>1</sup>	Conductor Gauge	No. of Pairs	Dimensions [inches]		Part
			Width	Height	Number
1.4	28 AWG	4	0.52	0.15	DC-601

### Note


1. Amp rating is the maximum value for each conductor at room temperature of 70°F (21°C). Amp rating decreases as temperature increases.

# **Cable Assemblies**



#### Please contact Cicoil for other connectors and length options

#### Assembly Dimensions



#### Notes

- 1. Append onto base cable Part Number for complete assembly
- 2. Connector ratings may differ from cable ratings; refer to manufacturer

# Wiring Diagram

0.15

Dimensions -SHIELDED PAIRS 00000

0.52



Options

# Cable Specifications

All engineering values are nominal and subject to change.

Mechanical	Environmental	Additional Conductors	
Conductors: Ultra flexible, finely stranded, tinned copper Shielding: Ultra flexible, braided shields, with 90% nominal coverage	Moisture Rating: Submersible, Salt Water Resistant StripMount™ Inter   Clean Room Rating: Class 1, Zero Particulates Integrated Tubing   Extreme Environments: Sunlight, UV Light, Alcohol, Chemical and Oil Resistant SuperTuff™ Jacket   Colored Jacket Disloction Strip Streamth, 4E0 wolts/(mil) Colored Jacketing	Low Friction Options StripMount™ Integrated Mounting Strip Integrated Tubing	
Minimum Bend Radius: - 6x cable height for intermediate flex - 10x cable height for continuous flex		SuperTuff™ Jacket Colored Jacketing	
Flex Life: 10,000,000 cycles nominal Outer Jacket Durometer Rating: 65 (Shore A)	See Electrical Rating Chart on Page 47	Strip and Tin Cable Ends FlexRail™ Self-Supporting Cable Complete Assembly	

- Example: DC-601-CA003
- specifications.

Flexible Flat Cables & Cable Assemblies 10

Ethernet / p1of1 / 2019-10-09

661-295-1295 Cicoil.com