

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0151340702**  
**Status:** **Active**  
**Overview:** PicoBlade Connector System  
**Description:** PicoBlade Female-to-PicoBlade Female Off-the-Shelf (OTS) Cable Assembly, Single Row, 150.00mm Length, 7 Circuits, Natural

**Documents:**

|                                |  |
|--------------------------------|--|
| <a href="#">3D Model</a>       | <a href="#">Datasheet (PDF)</a>                      |
| <a href="#">3D Model (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a> |
| <a href="#">Drawing (PDF)</a>  |  |

**General**

|                        |                                     |
|------------------------|-------------------------------------|
| Product Family         | Cable Assemblies                    |
| Series                 | <u>15134</u>                        |
| Application            | Signal, Wire-to-Board, Wire-to-Wire |
| Assembly Configuration | Dual Ended Connectors               |
| Connector to Connector | PicoBlade-to-PicoBlade              |
| Overmolded             | No                                  |
| Overview               | <u>PicoBlade Connector System</u>   |
| Product Name           | PicoBlade                           |
| Type                   | Discrete Wire Assembly              |
| UPC                    | 889056872065                        |

**Physical**

|                                |                      |
|--------------------------------|----------------------|
| Cable Length                   | 150.00mm             |
| Circuits (Loaded)              | 7                    |
| Color - Resin                  | Natural              |
| Gender                         | Female-Female        |
| Lock to Mating Part            | Yes                  |
| Material - Metal               | Phosphor Bronze      |
| Material - Plating Mating      | Tin                  |
| Material - Plating Termination | Tin                  |
| Material - Resin               | Polyester            |
| Net Weight                     | 2.325/g              |
| Number of Rows                 | 1                    |
| Packaging Type                 | Bag                  |
| Pitch - Mating Interface       | 1.25mm               |
| Plating min - Mating           | 0.889µm              |
| Plating min - Termination      | 0.914µm              |
| Single Ended                   | No                   |
| Termination Interface: Style   | Crimp or Compression |
| Wire Insulation Diameter       | 0.90mm               |
| Wire Size AWG                  | 28                   |
| Wire/Cable Type                | UL 1061              |


**Electrical**

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 1.0A |
| Voltage - Maximum             | 125V |

**Material Info**

**Reference - Drawing Numbers**

|               |                |
|---------------|----------------|
| Sales Drawing | 2012341359-000 |
|---------------|----------------|



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

15134 Series

**Mates With**

PicoBlade Header [53261](#) , [53047](#) , [53398](#) ,  
[53048](#) . PicoBlade Plug Housing [51047](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15134-0702](#)