


APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/16/13	



SPECIFICATIONS:
 Material:
 Insulator: PA66, rated UL 94V-0
 Insulator color: Green
 Wire guard: Brass, Tin plated
 Screw: Steel, M3.0/Zinc plated
 Clamp: Phosphor Bronze, Nickel plated
 Electrical:
 Voltage rated: 300 VAC
 Current rated: 15 Amps
 Contact resistance: 20 mΩ
 Insulation resistance: 500 MΩ @ 500 VDC
 Withstanding voltage: 2000V AC/1 Min
 Mechanical:
 Solid wire: 28-14AWG 2.5mm²
 Torque (Lb-In): 0.5Nm (4.5lb-in)
 Strip length: 7-8mm
 Temperature Rating:
 Operating temperature: -40°C to +105°C
 Environmental:
 Lead free, RoHS compliant.



Poles: 2 thru 24
 A = .200 [5.08] x No. of Poles
 B = .200 [5.08] x No. of (Poles - 1)

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED			
INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

APPROVALS		DATE
DRAWN	AY	10/16/13
CHECKED	NP	10/16/13
APPROVED		

TITLE .197 [5.08] TERMINAL BLOCK, SLOTTED SCREW			
SIZE X	PART NO. EBHA-XX-D	REV. -	
REF: S00067C	SCALE: NTS	SHEET 1 OF 1	