




APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	08/01/13	
A		UPDATED SPEC.	7/20/15	HR/AY



Positions: 02 thru 24
 A = .200 [5.08] x No. of Positions + .055 [1.40]
 B = .200 [5.08] x No. of Spoces

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: TERMINAL BLOCK, SOCKETS .200 [5.08] PITCH
 VERTICAL, CLOSE TYPE

SPECIFICATIONS:
 Material: Insulator: PA66, rated UL 94V-0
 Insulator color: Green
 Contact: Brass, Tin plated.
 Electrical:
 Operation voltage: 300 VAC max
 Current rating: 15 Amps
 Contact resistance: 20 mohms max
 Insulation resistance: 500 Mohms min @ 500 VDC
 Dielectric withstanding voltage: 2,000 VAC for 1 minute
 Temperature Rating:
 Operating temperature: -40°C to +105°C
 Environmental:
 Lead free, RoHS compliant.

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED			
.X	± .10	ØX	± .10
.XX	± .020	ØXXX	± .015
.XXX	± .015	ØXXXX	± .010
APPROVALS		DATE	
DRAWN	AY		10/17/13
CHECKED	NP		10/17/13
APPROVED			

SIZE	PART NO.	REV.
X	EBPA-XX-D-C	A
REF:	S00067C	SCALE: NTS
SHEET 1 OF 1		

