


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20  
 © COPYRIGHT 20 ALL RIGHTS RESERVED.

| LOC | DIST | REVISIONS |     |                           |           |     |      |
|-----|------|-----------|-----|---------------------------|-----------|-----|------|
| CM  | 00   | P         | LTR | DESCRIPTION               | DATE      | DWN | APVD |
|     |      | P2        |     | REVISED PER ECR-17-004864 | 21APR2017 | N.L | D.Z  |

1. ACCEPTS CONTACT P/N 1375819.
2. ACCEPTS MTA-100 KEYING PLUG P/N 641994-1.
3. DIMENSIONS IN BRACKETS ARE IN INCHES.
4. NOT FOR USE WITH CONTACT PART NUMBER 770601 OR 770666.



| mm                                 | INCH  | NO OF CKTS | PART NO     |
|------------------------------------|-------|------------|-------------|
| 71.63                              | 2.820 | 28         | 2-1375820-8 |
| 69.09                              | 2.720 | 27         | 2-1375820-7 |
| 66.55                              | 2.620 | 26         | 2-1375820-6 |
| 64.01                              | 2.520 | 25         | 2-1375820-5 |
| 61.47                              | 2.420 | 24         | 2-1375820-4 |
| 58.93                              | 2.320 | 23         | 2-1375820-3 |
| 56.39                              | 2.220 | 22         | 2-1375820-2 |
| 53.85                              | 2.120 | 21         | 2-1375820-1 |
| 51.31                              | 2.020 | 20         | 2-1375820-0 |
| 48.77                              | 1.920 | 19         | 1-1375820-9 |
| 46.23                              | 1.820 | 18         | 1-1375820-8 |
| 43.69                              | 1.720 | 17         | 1-1375820-7 |
| 41.15                              | 1.620 | 16         | 1-1375820-6 |
| 38.61                              | 1.520 | 15         | 1-1375820-5 |
| 36.07                              | 1.420 | 14         | 1-1375820-4 |
| 33.53                              | 1.320 | 13         | 1-1375820-3 |
| 30.99                              | 1.220 | 12         | 1-1375820-2 |
| 28.45                              | 1.120 | 11         | 1-1375820-1 |
| 25.91                              | 1.020 | 10         | 1-1375820-0 |
| 23.37                              | .920  | 9          | 1375820-9   |
| 20.83                              | .820  | 8          | 1375820-8   |
| 18.29                              | .720  | 7          | 1375820-7   |
| 15.75                              | .620  | 6          | 1375820-6   |
| 13.21                              | .520  | 5          | 1375820-5   |
| 10.67                              | .420  | 4          | 1375820-4   |
| 8.13                               | .320  | 3          | 1375820-3   |
| 5.59                               | .220  | 2          | 1375820-2   |
| DIM A +0.25/-0.13<br>[+.010/-.005] |       |            |             |



METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.

|                            |  |                   |   |   |             |  |
|----------------------------|--|-------------------|---|---|-------------|--|
| DIMENSIONS:<br>mm [INCHES] | TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0 PLC ±<br>1 PLC ±<br>2 PLC ±0.13 [.005]<br>3 PLC ±<br>4 PLC ±<br>ANGLES ±<br>FINISH | MATERIAL<br>NYLON | DWN K. WHITAKER 21-JUNE-2001<br>CHK J. ELLIS 21-JUNE-2001<br>APVD J. ELLIS 21-JUNE-2001 | PRODUCT SPEC<br>108-1948<br>APPLICATION SPEC<br>114-13036 | WEIGHT<br>- | TE Connectivity<br>NAME<br>HOUSING, CST-100 II<br>SIZE CAGE CODE DRAWING NO<br>A200779 C-1375820<br>RESTRICTED TO<br>- |
|----------------------------|--|-------------------|---|---|-------------|--|

CUSTOMER DRAWING SCALE 8:1 SHEET 1 OF 1 REV P2

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1375820-8](#)