



21 90 03

Reducing Bushes short pattern, PVC-U

with spigot and solvent socket



d - d ₁	PN	Code	£	SP	GP	g	z	l
12- 8	16	721.900.329	0.40	10	1200	2	2	14
16- 12	16	721.900.331	0.40	10	1000	2	2	14
20- 16	16	721.900.334	0.58	10	500	2	2	16
25- 20	16	721.900.337	0.75	10	450	5	3	19
32- 20	16	721.900.342	0.97	10	100	14	6	22
32- 25	16	721.900.341	0.97	10	100	9	3	22
40- 20	16	721.900.348	1.30	10	150	22	10	26
40- 25	16	721.900.347	1.30	10	100	21	7	26
40- 32	16	721.900.346	1.30	10	100	17	4	26
50- 32	16	721.900.353	1.65	10	100	40	9	31
50- 40	16	721.900.352	1.65	10	100	30	5	31
63- 32	16	721.900.360	2.20	10	100	61	16	38
63- 40	16	721.900.359	2.20	10	100	66	12	38
63- 50	16	721.900.358	2.20	10	100	50	7	38
75- 50	16	721.900.365	3.85	10	50	117	13	44
75- 63	16	721.900.364	3.85	10	50	80	6	44
90- 50	16	721.900.372	6.20	10	10	180	20	51
90- 63	16	721.900.371	6.20	10	10	180	13	51
90- 75	16	721.900.370	6.75	10	10	145	7	51
110- 50	16	721.900.379	8.50	5	5	260	30	61
110- 63	16	721.900.378	8.50	5	5	320	23	61
110- 90	16	721.900.376	8.50	5	5	260	10	61
125- 90	16	721.900.381	14.50	5	5	442	18	69
125-110	16	721.900.380	14.50	5	5	265	8	69
140- 90	16	721.900.386	24.50	5	5	580	25	76
140-110	16	721.900.385	24.50	5	5	580	15	76
140-125	16	721.900.384	24.50	5	5	420	7	76
160- 90	16	721.900.391	26.40	5	5	770	35	86
160-110	16	721.900.390	26.40	5	5	870	25	86
160-140	16	721.900.388	31.90	5	5	560	10	86
200-110	10	721.900.393	38.60	3	3	1900	45	106
200-125	10	721.900.325	38.60	3	3	1940	37	106
200-140	10	721.900.394	38.60	3	3	1850	30	106
200-160	10	721.900.392	38.60	2	2	1100	20	106
225-110	10	721.900.397	56.50	3	3	2450	58	119
225-125	10	721.900.399	56.50	4	4	2500	50	119
225-140	10	721.900.398	56.50	3	3	2500	43	119
225-160	10	721.900.396	56.50	2	2	2200	33	119
225-200	10	721.900.181	56.50	1	1	1400	13	119
250-125	10	721.900.326	91.80	4	4	3150	62	131
250-140	10	721.900.300	91.80	3	3	3200	55	131
250-160	10	721.900.301	91.80	3	3	2450	45	131
250-200	10	721.900.302	91.80	3	3	3150	25	131
250-225	10	721.900.303	103.10	1	1	1700	12	131
280-140	10	721.900.307	142.40	1	1	4000	69	148
280-160	10	721.900.308	142.40	1	1	4100	59	148
280-200	10	721.900.304	142.40	1	1	4250	40	146
280-225	10	721.900.305	142.40	1	1	4300	27	146
280-250	10	721.900.306	142.40	1	1	2500	15	146
315-160	10	721.900.313	142.40	1	1	2050	77	166
315-200	10	721.900.309	153.50	1	1	5300	57	166
315-225	10	721.900.310	153.50	1	1	5500	45	164
315-250	10	721.900.311	153.50	1	1	6300	33	164
315-280	10	721.900.312	153.50	1	1	3550	17	164
355-315	6	721.900.315	162.00	1	1	5300	20	184
400-250	6	721.900.319	175.00	1	1	9000	75	206
400-280	6	721.900.320	175.00	1	1	9200	60	206
400-315	6	721.900.321	175.00	1	1	13100	42	206
400-355	6	721.900.322	175.00	1	1	7600	22	206

PVC-U