

0 601 063 R00 – GLL 3-80 C

Material number	0 601 063 R03
EAN	3165140888288
1 x battery GBA 12V 2.0 Ah 1 600 Z00 02X	
4 x 1.5 V LR6 AA	✓
AA1 alkaline battery adapter 1 608 M00 C1B	✓
BM 1 Professional universal mount 0 601 015 A01	✓
L-BOXX 136 1 600 A00 1RR	
Laser target plate	✓
Pouch	✓
Quick charger GAL 1230 CV 1 600 A01 16B	



Laser diode	Line: 630 - 650 nm, < 10mW
Operating temperature	-10 – 40 °C
Storage temperature	-20 – 70 °C
Laser class	2
Working range	30 m
Working range with receiver	120 m
Working range without receiver	30 m
Accuracy	± 0.2 mm/m
Self-levelling range	± 4°
Levelling time	4 s
Dust and splash protection	IP 54
Power supply	12 V Li-Ion battery 4 x 1.5 V LR6 (AA)
Operating time (max.)	8 h (Li-Ion) and 6 h (4 x AA) in 3-line mode


Tripod thread	1/4", 5/8"
Weight, approx.	0.9 kg
Colour of laser line	red
Projection	3 x 360° line

Technical data

Description

Outdoor applications	Alignment Pulse mode
Indoor applications	Drywall installation Suspended ceiling installation Interior fitting work Levelling work Floor and wall tiles Fitting cabinets and shelves

Technical data



Sales information

Positioning

- Visibility on a new level in 3 x 360°. Simply Connected.

User benefit

- High precision due to the innovative CAL Guard monitoring and Bluetooth® connection to your smartphone for remote control use and contactless adjustment of the tool
- High visibility due to high power diodes
- High work efficiency due to 3 x 360° lines: Simultaneous performance of horizontal and vertical levelling applications in the entire room with only one tool

Other features

- Dual Power Source: Can be operated both with 12 V LI-ion battery and with standard alkaline batteries
- Self-levelling ($\pm 4^\circ$ in <4 sec), very precise (± 0.2 mm/m) and range of up to 120 m with LR 6 or LR 7 Professional receiver (optional)
- Compact, easy to handle and extremely robust (IP54)
- Pendulum lock ensures safe transport