



Datenblatt - Fiche technique - Data sheet

**12.03.3205**




ROLINE Typ C - DVI Adapter, ST/BU

ROLINE Adaptateur Type C - DVI, M/F

ROLINE Type C - DVI Adapter, M/F

Item no.: 12.03.3205

## ROLINE USB 3.1 Cable Adapter, C – DVI (24+5), M/F Aluminum, silver



### Features:

- Support DVI (24+5) Video output 1920\*1080@60 Hz resolution
- Aluminum Housing in silver color
- No driver needed
- USB 3.1 Type-C interface supports plug and play, hot swap
- Easy to carry and use
- With 10cm Cable in white color
- Connector: USB 3.1 Type-C Male\*1 (input) + DVI(24+5) Female\*1 (output)
- Operating Temperature: 0°C ~45°C
- Storage Temperature: -20°C ~ 70°C
- Operating Humidity: 10% ~ 85 % RH (no condensation)
- System requirements: Windows, MAC OS X, Google Chrome

# USB 3.1 Type-C™ to DVI 24+5

## Socket Converter

### User Manual



# Contents

1.0 INTRODUCTION.....	1
2.0 FEATURES .....	1
3.0 SPECIFICATIONS .....	1
4.0 PACKAGE CONTENTS.....	2
5.0 OPERATION .....	2
6.0 CONNECTION DIAGRAM .....	2

# USB 3.1 Type-C™ to DVI 24+5 Socket converter

## DEAR CUSTOMER

Thank you for purchasing this product. For optimum performance and safety, please read these instructions carefully before connecting, operating or using this product. Please keep this manual for future reference.

## 1.0 INTRODUCTION

This is a USB 3.1 Type C™ to DVI24+5 Socket, designed for connecting DVI Monitor to host computer, the host computer can easily connect to the DVI Monitor. Connecting the monitor with a DVI cable which is contacted with DVI socket of this converter It can work on Macbook or Google new Chromebook Pixel or Asus Zen AiO and other USB 3.1 Type C™ supported devices.

## 2.0 FEATURES

- Support USB 3.1 Type C™ Video output 1920\*1080@60hz resolution
- NO driver needed
- ABS Housing
- With 10cm Cable
- USB 3.1 Type C™ interfaces support plug and play, hot swap
- Easy to carry and use

## 3.0 SPECIFICATIONS

<b>Item No.:</b>	
ABS Housing	716107 716107S
Aluminium Housing	716107V 716107D 716107X
<b>Size(L*W*H)</b>	200*48*14mm
<b>Input/Output Connector</b>	
Input port	USB 3.1 Type C™ Male*1
Output port	DVI24+5 Socket
<b>Warranty</b>	
Limited Warranty	1 Year
<b>Environmental</b>	
Operating Temperature	0°C ~ 45°C
Operating Humidity	10% ~ 85 % RH (no condensation)
Storage Temperature	-20°C ~ 70°C

Storage Humidity	5% ~ 90 % RH (no condensation)
<b>System requirements</b>	Windows, MAC OSX, Google Chrome
<b>Regulatory Approvals</b>	
	FCC CE Certification
	RoHS 2.0 & REACH Compliant
<b>Accessories Adapter</b>	
User Manual	English Version

## 4.0 PACKAGE CONTENTS

Before attempting to use this unit, please check the packaging and make sure the following items are contained in the shipping carton:

- Main unit x1
- User Manual x1

## 5.0 OPERATION

- 1) Connect the DVI 24+5 Socket to DVI Monitor
- 2) Connect the USB 3.1 Type C™ male port of this product to computer

## 6.0 CONNECTION DIAGRAM

