

_			2			3						
	REFERENCE FOR REEL ACCORDING TO FEEDING DIRECTION											
А	GAUGE	REEL OF 5000 F	EMALE CONT	TACTS	GAUGE	REEL OF 5000 PIN CONTA	С					
	# 24-28	86566610064LF			# 24-28	86564610064LF						
	# 20-24	86566620064LF			# 20-24	86564620064LF						
	# 24-28	86566610065LF			# 24-28	86564610065LF						
	# 20-24	86566620065LF			# 20-24	86564620065LF						
	# 24-28	86566610067LF			# 24-28	86564610067LF						
	# 20-24	865666	20067LF		# 20-24	86564620067LF						


-Ø200mm

-Ø450mm



Ø25mm-






The cou Ter	NOTE : ROHS INFORMATIONS The LF products meet European union directives and other country regulations as described in GS-47-0004 Terminations plating spec : I.3um Nickel min + I.3um Sn min Packaging Spec : see GS-14-920		specref -			dr	P-Mathew Neb	u	2011/05/17		projec	tion	
		tolerance std	rance std				Paul Mithun		2019/03/18				
		0004	ISO 406	I TOLEH	ANCES UNLESS /ISE SPECIFIED		chr	-		-			
			ISO   0				appr	K-Paul Biju		2019/03/19		product f	amily
				linear	0.X	±0.3	Amphanal		° ∩ D	RIMP PIN		8 SOCKET	
			surface -/		0.XX	±0.1	Amj	FCi				S SUCREI	
					0.XXX	±0.05		FUI	+ 20-	-28AWG,	5000	Reel Qty	ł
			ISO I302	angular	0°	±2°			cat. no	0.		-	

C 2016 AFCI

D

2



А В

Printed: Mar 19, 2019