



2403E

Product no.: 2403E

Tip cutter - angled wide robust head. Oval shape



The angled head provides for precise cuts at different working angles.



Similar to 503E, but with ergonomic handles



source images

The Perfect Cut - Strong, sharp and precise, every time

The Weller Erem Series 2400 Magic Sense is a range of medium-sized precision cutters that combines robustness, visibility and accessibility. A large variety of head shapes for precision work in hard-to-reach areas. The optimized ergonomic shape of the Series 2400 MagicSense prevents hand fatigue. These cutters are manufactured from improved induction-hardened cutting edges up to 64 – 65 HRC for an extremely long service life. The cutting edges are made from special tool steel. The precision cutters have a nonreflecting surface, are ESD safe and resharpenable.

		Type	Type of Cut	Cutting Capacity
Series 2400 MagicSense				mm 0,03 0,1 0,2 0,3 0,4 0,5 0,6 0,7 0,8 0,9 1,0 1,1 1,2 1,3 1,4 1,5 1,6 1,7 1,8 1,9 2,0 Inch .0001 .003 .007 .011 .015 .019 .023 .027 .031 .035 .039 .043 .047 .051 .055 .059 .062 .066 .070 .074 .078
	2412E		Semi Flush	0,1 - 1,6
	2422E		Flush	0,1 - 1,6
	2432E		Super Full Flush	0,1 - 1,6
	2477E		Flush	0,1 - 1,2
	2403E		Flush	0,1 - 1,6
	2404E		Flush	0,1 - 1,2
	2482E		Flush	0,1 - 1,2
	2475E		Flush	0,1 - 0,6
	2470E		Flush	0,1 - 0,6
	2476TX2		Flush / Carbide	0,1 - 1,2





Technical Data

Length mm	127
Length of cutting edges mm	9
Head width mm	11
Head thickness mm	6
Head length mm	20
Max. cutting capability – hard wire mm	---
Weight in oz	2.646
Length of cutting edges Inches	0.354
Head width Inches	0.433
Head thickness Inches	0.236
Head length Inches	0.787
ESD-safe	on
Cut	Flush
Max. cutting capability – medium hardness mm	Ø 1,0
Max. cutting capability – copper wire mm	Ø 1,6
Length inches	5
Weight in g	75
Erem applications	Microelectronic