

# HG 330-B

---

Hot-air blower



simple.  
good.  
affordable.

# HG 330-B: The compact Weldy hot-air blower

The HG 330-B hot-air gun is a high-performance Weldy hot-air blower with two fast temperature switching stages for selecting between 350 °C and 550 °C. This means it can meet the requirements of a wide range of specialist and home improvement tasks. Whether it is removing paint and varnish, refreshing plastic parts, loosening valves and fittings or de-icing pipes, the hot-air gun is a useful tool for various tasks that require hot air thanks to its low weight and comfortable handle.

Hot-air blower

## HG 330-B

- combines efficiency with solid performance
- two fast temperature switching stages
- reasonably priced entry-level unit for professionals and DIY enthusiasts
- well-suited for processing plastic films and plastic profiles



### Technical data

Voltage	V~	100	120	230
Max. power	W	1100	1200	1600
Temperature	°C	350 / 550	350 / 550	350 / 550
Air volume	l/min	250 / 400	250 / 400	350 / 500
Dimensions L × W × H	mm	250 × 80 × 230		
Weight	kg	0.7		
Conformity marking		CE		
Protection class II		□		

Only available as a kit (hot-air hand tool incl. accessories)



#### Kit HG 330-B

230 V / 1600 W, CN plug	124.403
230 V / 1600 W, EU plug	164.323
230 V / 1600 W, CH plug	134.690
230 V / 1600 W, UK plug	131.321
230 V / 1600 W, AUS plug	133.771
120 V / 1200 W, US plug, polarized (UL)	123.155
100 V / 1100 W, JP plug	120.128

#### Accessories (included in kit)

119.341 Glass protection nozzle	•
119.344 Spoon reflector	•
Carton tool packaging	•
Instruction manual	•



Händleradresse:



Leister Technologies AG ist **ISO 9001** zertifiziert.