



2X05P



P/N LEGEND

A1001	HB-2XNP	N	0	W	NP	N	00	G	
①	②	③	④	⑤	⑥	⑦	⑧	⑨	⑩

① Series No.
 ② Connector type: HB=Housing B Type
 ③ No. of circuits
 ④ N=Halogen Free
 ⑤ Material: 0=Nylon 66-V0+GF15%
 ⑥ Color: W=Natural(White)
 ⑦ Plating code: NP=Non-plating
 ⑧ Plating code: N=Non-plating
 ⑨ Option code: 00=Standard
 ⑩ Packing code: G=Bag

SPECIFICATIONS

Current Rating: 1A AC,DC
 Voltage Rating: 50V AC,DC
 Temperature Range: -25°C ~ +85°C
 Contact Resistance: 20mΩ Max.
 Insulation Resistance: 100MΩ Min.
 Withstanding Voltage: 500V AC/minute

Circuit No.	Dimensions		
	A	B	C
2X05P	4.00	8.00	5.35
2X06P	5.00	9.00	6.35
2X08P	7.00	11.00	8.35
2X09P	8.00	12.00	9.35
2X10P	9.00	13.00	10.35
2X15P	14.00	18.00	15.35
2X20P	19.00	23.00	20.35
2X25P	24.00	28.00	25.35

				燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.			
UNIT		SCALE		SHEET		TITLE:	
mm		1 : 1		1 of 1			
DRAWN BY		APPROVED BY				1.00mm PITCH HOUSING-DUAL ROW	
陳錦展		謝瑞清					
2012.12.12		2012.12.12					
A2		EN1309030320		2016.08.31		賴永強	
A1		EN1309030320		2013.08.15		郭木恩	
A0		NEW RELEASE		2012.12.12		陳錦展	
REV.		DESCRIPTION		DATE		NAME	
		GENERAL TOLERANCE		ANGLE±		DRAW NO. :	
		X. X±0.25		X. XX±0.15		A1001HB-2XNPXXXXXXXXXX	
		X. XXX±0.05				REV. A2	