

PIN RECEPTACLES

**FOR .048" - .064" DIAMETER PINS (#13 CONTACT)
FOR .045" - .065" DIAMETER PINS (#23 CONTACT)**

<p>8365 8365-0-15-XX-13-XX-10-0 Hex press-fit in .106 plated through-hole</p>	<p>8996 8996-0-31-XX-13-XX-04-0 Compliant press-fit in .040 ± .003 plated hole. For .060" → .100" thick board</p>	<p>9064 9064-0-15-XX-13-XX-10-0 Solder mount in .102 min. mounting hole Also available on 16mm wide carrier tape: 1,300 parts per 13" reel See page 194.14 for Tape & Reel details</p>	<p>9280 9280-0-15-XX-13-XX-10-0 Solder mount in .102 min. mounting hole</p>
<p>8347 8347-0-15-XX-13-XX-10-0 Solder mount in .109 min. mounting hole</p>	<p>4900 4900-0-19-XX-23-XX-10-0 Swage mount in .067 hole</p>	<p>0716 0716-0-33-XX-23-XX-10-0 Wire crimp termination. Accepts wire sizes 16 AWG Max. / 20 AWG Min.</p>	<p>0760 0760-0-18-XX-13-XX-10-0 Press-fit in .106 mounting hole For wire sizes up to 16 AWG</p>

SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard
Contact Material: Beryllium Copper Alloy 172, HT
Dimensions: Inches
Tolerances On: Lengths: ± .005
Diameters: ± .002
Angles: ± 2°



ORDER CODE: XXXX - X - XX - XX - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01 200 μ" TIN/LEAD OVER NICKEL
- ◆ 80 200 μ" TIN OVER NICKEL (RoHS)
- ◆ 15 10 μ" GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

- 01 200 μ" TIN/LEAD OVER NICKEL
- ◆ 80 200 μ" TIN OVER NICKEL (RoHS)
- ◆ 27 30 μ" GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#13 or #23 CONTACT (DATA ON PAGE 260)
(For alternate contact choices, see group G on page 248)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mill-Max:](#)

[9064-0-15-01-13-01-10-0](#) [9064-0-15-01-13-27-10-0](#) [9280-0-15-80-13-80-10-0](#) [9064-0-15-80-13-27-10-0](#) [9064-0-15-15-13-27-10-0](#) [0716-0-33-15-23-27-10-0](#) [0760-0-18-80-13-27-10-0](#) [9280-0-15-15-13-14-10-0](#) [8347-0-15-15-13-27-10-0](#)