



Part Number : PTC 130/30
Proximity Switch - Reed Switch based
Threaded - Change Over Contacts - Suggested Magnet: PRM
Product Data Sheet

PICTURE	DIMENSIONS	Applications Include	
	 <p>300 (11.811)</p> <p>28 (1.102)</p> <p>2 x M6 Nuts</p> <p>M6 thread</p>	<ul style="list-style-type: none"> ● Position and limit sensing. ● Linear actuators . ● Security system switch. ● Door Switch. 	
<p>✓ RoHS Compliant</p> <p>Drawings not to scale All dimensions in mm(inches) nominal</p>		<th data-bbox="957 719 1533 752">Options</th> <ul style="list-style-type: none"> ● M6 Thread. ● Custom cable lengths, strip lengths, cable types, terminations. ● If you do not see what you need, just ask, as there is a strong possibility we can do it ! 	Options

SPECIFICATION	
Contact Form / Style	Change Over
Switching Capacity (Resistive)	5 W/VA Max.
Switching Voltage	100 VAC Max.
Switching Current	0.5 A. Max.
Carry Current	1.0 A. Max.
Breakdown Voltage	200 VDC Min.
Contact Resistance	150 mOhms Max.
Switching Distance	3 mm Min.
Operating Temperature Range	-20°C +85°C
Storage temperature	-25°C +90°C
Case Material	Brass-Nickel Plated
Cable	3 x Round 0.22mm ² PVC Insulated Brown / White / Green

Rev. No.	Revision Note	Date	Signature
2	Datasheet Redesign	28-07-06	LG



As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and the details of our full design and manufacturing service. All products are supplied to our standard conditions of sale unless otherwise agreed in writing.

Phone : +44 (0)1255 862236 www.assemtech.co.uk Fax: +44 (0)1255 862014

©2006 Copyright Assemtech Europe Ltd, Unit 7, Rice Bridge Industrial Estate, Thorpe - Le - Soken, Essex, CO16 0HL, ENGLAND.
USA: + 1 973 777 6900 - Belgium: + 32 (0)12 390400 - France: + 33 (0) 1 43 96 86 10