


Inductor TCK-108


Order Code	TCK-108
Inductance	<b>3.3 μH ±20%</b> (at 100 kHz / 250 mV)
Impedance (DCR)	50 mΩ max.
Rated Current	3.3 A max.
Operating Temperature	-40°C to +125°C




## Impedance Curve



## **Outline Dimensions**





Dimensions [mm]	
Α	4.0 ±0.3
В	4.0 ±0.3
С	2.1 max.
D	4.7 max.
E	1.0 ±0.3
F	0.6 ±0.1
G	2.2
Н	6.0
I	1.5