

D-SUB bus connector - Subcon 15 HD/M-SH - 5604602

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



D-SUB connector, 15-pos, male connector, one cable entry < 35°, universal type for all systems, pin assignment: 1, 2, 3, ..., 14, 15 to screw connection terminal block

Key commercial data

Packing unit	1 pc
Weight per Piece (excluding packing)	0.77 g
Custom tariff number	85366990

Technical data

Dimensions

Max. cable diameter	12.7 mm
Min. cable diameter	4 mm
Width	16 mm
Height	49.8 mm
Length	61 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 75 °C
---------------------------------	------------------

General

Nominal voltage U_N	48 V AC/DC
Nominal current I_N	1 A
Signal	Point-to-point
Insertion/withdrawal cycles	> 50
SUBCON fixing screws	4-40 UNC
Tightening torque	0.4 Nm
Housing material	ABS, metal-plated
Pin assignment	All connections are 1:1 on the screw terminal block

Connection data

Connection	D-SUB connection
Number of positions	15
Connection method	D-SUB connector

D-SUB bus connector - Subcon 15 HD/M-SH - 5604602

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440302

ETIM

ETIM 3.0	EC001132
ETIM 4.0	EC001132
ETIM 5.0	EC001132

UNSPSC

UNSPSC 6.01	30211802
UNSPSC 7.0901	39121402
UNSPSC 11	39121402
UNSPSC 12.01	39121402
UNSPSC 13.2	39121402